Adjust-A-Box® Adjustable Zip Boxes and Brackets - Nonmetallic





The Carlon Adjust-A-Box® features a patented design that allows the box to be adjusted to most wall thicknesses with the turn of a screw. To install, simply clip the bracket onto the stud, secure with two screws to ensure the box won't move, then turn the adjustment screw clockwise or counterclockwise, and adjust the box flush with the wall covering.

The Adjust-A-Box is available in one- and two-gang versions, and by removing the box from the bracket the one-gang box can easily be upgraded to a two-gang box, an ideal feature for old work applications.

The Carlon Adjust-A-Box achieves professional results every time.

Features

- Patented adjustment screw that adjusts from 0'' to $1^{3/4}''$
- Ideal for new work or retrofit applications
- Available in backed box or backless bracket designs
- Upgrades made easy
- Nonmetallic and durable
- UL Listed
- Meets NEMA OS-2



One-Gang and Two-Gang — High Voltage

	Part No.	Volume (cu. in.)	Description	Size	Std. Ctn. Qty.	Std. Ctn. Wt. (lbs.)
	B121ADJ	21	One-Gang Adjustable Wall Box	3 ⁷ /8"W x 3 ³ /4"H x 3 ³ /8"D	24	10
	B234ADJC	34	Two-Gang Adjustable Wall Box w/ Range Knockout	5 ⁵ /8"W x 3 ⁵ /8"H x 3"D	16	8.5
	B234ADJ	34	Two-Gang Adjustable Wall Box	5 ⁵ /8"W x 3 ⁵ /8"H x 3"D	16	8.5

B121ADJ

SC100ADJC





www.carlon.com